Capsule pressure gauge, copper alloy Plastic case Model 611.13, NS 50 [2"], 63 [2 ½"]

WIKA data sheet PM 06.12







For further approvals, see page 6



Applications

- Pressure gauge for use in a protected environment
- Medical, vacuum, environmental, laboratory technology, for contents measurement and filter monitoring
- For gaseous, dry and non-aggressive media

Special features

- Compact design and ingress protection IP53
- Case from plastic
- Special connection location on request
- Low scale ranges from 0 ... 60 mbar to 0 ... 1,000 mbar or 0 ... 24 inH₂O to 0 ... 400 inH₂O



Capsule pressure gauge model 611.13

Description

The model 611.13 capsule pressure gauge is based upon the proven capsule measuring system. One half of the capsule element forms the plastic case and the other half is made of a copper-beryllium alloy (CuBe).

The capsule element measurement principle is suitable for very low pressures. On pressurisation, the expansion of the capsule element, proportional to the incident pressure, is transmitted to the movement and indicated.

The modular design enables a multitude of customer-specific applications. The model 611.13 instrument is used with great success, particularly in medical engineering applications.

The scale ranges of 0 ... 60 mbar to 0 ... 1,000 mbar or 0 ... 24 inH $_2$ O to 0 ... 400 inH $_2$ O and the vacuum and +/- scale ranges ensure the measuring ranges required for a wide variety of applications.

WIKA data sheet PM 06.12 \cdot 11/2023





Specifications

Basic information	
Standard	EN 837-3
	→ For information on the "Selection, installation, handling and operation of pressure gauges", see technical information IN 00.05
Further version	Oil- and grease-free
Nominal size (NS)	■ Ø 50 mm [2"] ■ Ø 63 mm [2 ½"]
Connection location	Lower mount (radial)Centre back mount
Window	Plastic, crystal-clear, snap-fitted in case
Case	Plastic, black
Movement	Copper alloy

¹⁾ Only for back mount

Measuring element	
Type of measuring element	Capsule element
Material (wetted)	
Capsule element	CuBe alloy (copper-beryllium)
Case	Plastic, black
Sealing	NBR and silicone
Process connection	Copper alloy
Leak tightness	 Leakage rate: < 1 · 10⁻³ mbar l/s Helium tested, leakage rate: < 1 · 10⁻⁵ mbar l/s

Accuracy specifications	
Accuracy class	
EN 837-3	Class 2.5
ASME B40.100	■ ±3 % ±2 % ±3 % of measuring span (grade B)
Zero point setting with adjustment screw 1)	WithoutIn front, after opening the window
Temperature error	On deviation from the reference conditions at the measuring system: $\leq \pm 0.6$ % per 10 °C [$\leq \pm 0.6$ % per 18 °F] of full scale value
Reference conditions	
Ambient temperature	+20 °C [+68 °F]

¹⁾ Instruments with +/- scale range always feature zero point setting.

Other accuracy classes on request

Scale ranges

mbar	
0 60	0 250
0 100	0 400
0 160	0 600
0 200	0 1,000

kg/cm ²	
0 0.06	0 0.25
0 0.1	0 0.4
0 0.16	0 0.6
0 0.2	0 1

kPa	
0 6	0 25
0 10	0 40
0 16	0 60
0 20	0 100

Pa	
0 6,000	0 25,000
0 10,000	0 40,000
0 16,000	0 60,000
0 20,000	0 100,000

psi	
0 1	0 3.6
0 1.5	06
0 2.5	0 10
03	0 15

mmH ₂ O	
0 600	0 2,500
0 1,000	0 4,000
0 1,600	0 6,000
0 2,000	0 10,000

inH ₂ O	
0 24	0 100
0 40	0 160
0 60	0 240
0 80	0 400

oz/in²	
0 15	0 60
0 25	0 100
0 40	0 150
050	0 240

Vacuum and +/- scale ranges

mbar	
-60 0	-30 +30
-100 0	-50 +50
-160 0	-80 +80
-250 0	-125 +125
-400 0	-200 +200
-600 0	-300 +300
-1,000 0	-500 +500

kg/cm ²	
-0.06 0	-0.03 +0.03
-0.1 0	-0.05 +0.05
-0.16 0	-0.08 +0.08
-0.25 0	-0.125 +0.125
-0.4 0	-0.2 +0.2
-0.6 0	-0.3 +0.3
-1 0	-0.5 +0.5

kPa	
-6 0	-3 +3
-10 0	-5 + 5
-16 0	-8 +8
-25 0	-12.5 +12.5
-40 0	-20 +20
-60 0	-30 +30
-100 0	-50 +50

Pa	
-6,000 0	-3,000 +3,000
-10,000 0	-5,000 +5,000
-16,000 0	-8,000 +8,000
-25,000 0	-12,500 +12,500
-40,000 0	-20,000 +20,000
-60,000 0	-30,000 +30,000
-100,000 0	-50,000 +50,000

psi	
-1 0	-0.5 +0.5
-1.5 0	-0.75 +0.75
-2.5 0	-1.25 +1.25
-3.6 0	-1.8 +1.8
-6 0	-3 +3
-10 0	-5 +5
-15 0	-7.5 +7.5

mmH ₂ O	
-600 0	-300 +300
-1,000 0	-500 +500
-1,600 0	-800 +800
-2,500 0	-1,250 +1,250
-4,000 0	-2,000 +2,000
-6,000 0	-3,000 +3,000
-10,000 0	-5,000 + 5,000

inH ₂ O	
-24 0	-12 +12
-40 0	-20 +20
-60 0	-30 +30
-100 0	-50 +50
-160 0	-80 +80
-240 0	-120 +120
-240 0	-120 +120

oz/in²	
-15 0	-7.5 +7.5
-25 0	-12.5 +12.5
-40 0	-20 +20
-60 0	-30 +30
-100 0	-50 +50
-150 0	-75 +75
-240 0	-120 +120

Further details on: Scale ranges			
Unit	 mbar kg/cm² kPa Pa 	 ■ psi ■ mmH₂O ■ inH₂O ■ oz/in² 	
	Other units on request		
Overpressure safety	On request		
Vacuum safety	On request		
Dial			
Scale layout	Single scaleDual scale		
Scale colour	Single scale	Black	
	Dual scale	Black/red	
Serial number	■ Without ■ Consecutive number * *		
Material	Aluminium		
Special scale	Other scales or customer-specific dials, e.g. with red mark, circular arcs or circular sectors, on request		
Instrument pointer	Aluminium, black		
Pointer stop pin	WithoutAt zero pointAt 6 o'clock		

Process connection		
Standard	■ EN 837-3 ■ ANSI/B1.20.1	
Size		
EN 837-3	■ G 1/8 B, male thread■ G 1/4 B, male thread	
ANSI/B1.20.1	 ½ NPT, male thread ¼ NPT, male thread 	
Restrictor	 ■ Without ■ Ø 0.5 mm [0.02"], copper alloy ■ Ø 0.3 mm [0.012"], copper alloy 	
Material (wetted)		
Capsule element	CuBe alloy (copper-beryllium)	
Case	Plastic, black	
Sealing	NBR and silicone	
Process connection	Copper alloy	

Other process connections on request

Operating conditions	
Medium temperature	-20 +60 °C [-4 +140 °F]
Ambient temperature	-20 +60 °C [-4 +140 °F]
Pressure limitation	
Steady	Full scale value
Fluctuating	0.9 x full scale value
Short time	1.3 x full scale value
Ingress protection per IEC/EN 60529	IP53

Approvals

Logo	Description	Region	
CE	EU declaration of conformity	European Union	
	Pressure Equipment Directive PS > 200 bar, module A, pressure accessory		
	RoHS directive		
UK	UKCA	United Kingdom	
CA	Pressure equipment (safety) regulations		
	Restriction of hazardous substances (RoHS) regulations		

Optional approvals


Logo	Description	Region
6	PAC Kazakhstan Metrology, measurement technology	Kazakhstan
-	MChS Permission for commissioning	Kazakhstan
-	PAC Ukraine Metrology, measurement technology	Ukraine
	PAC Uzbekistan Metrology, measurement technology	Uzbekistan
-	CPA Metrology, measurement technology	China

Certificates (option)

Certificates					
Certificates	 2.2 test report per EN 10204 (e.g. state-of-the-art manufacturing, indication accuracy) 3.1 inspection certificate per EN 10204 (e.g. material proof for wetted metal parts, indication accuracy) 				
Recommended calibration interval	1 year (dependent on conditions of use)				

 $[\]rightarrow$ For approvals and certificates, see website

Dimensions in mm [in]




NS	Weight
50 [2"]	Approx. 0.07 kg [0.15 lb]
63 [2½"]	Approx. 0.08 kg [0.18 lb]

Process connection with thread per EN 837-3

NS	G	Dimensions in mm [in]				
		h ±1 [0.04]	а	b	D	sw
50 [2"]	G 1/8 B	45 [1.77]	9 [0.37]	35 [1.38]	49 [1.93]	14 [0.55]
	G 1/4 B	48 [1.89]	9 [0.37]	35 [1.38]	49 [1.93]	14 [0.55]
63 [2 ½"]	G 1/8 B	51.5 [2.03]	9.5 [0.37]	35 [1.38]	62 [2.44]	14 [0.55]
	G 1/4 B	54.5 [2.15]	9.5 [0.37]	35 [1.38]	62 [2.44]	14 [0.55]

Process connection with thread per ANSI/B1.20.1

NS	G	Dimensions in mm [in]					
		h ±1 [0.04]	а	b	D	sw	
50 [2"]	1/8 NPT	45 [1.77]	9 [0.37]	35 [1.38]	49 [1.93]	14 [0.55]	
	1/4 NPT	48 [1.89]	9 [0.37]	35 [1.38]	49 [1.93]	14 [0.55]	
63 [2 ½"]	1/8 NPT	51.5 [2.03]	9.5 [0.37]	35 [1.38]	62 [2.44]	14 [0.55]	
	1/4 NPT	54.5 [2.15]	9.5 [0.37]	35 [1.38]	62 [2.44]	14 [0.55]	



NS	Weight
50 [2"]	Approx. 0.07 kg [0.15 lb]
63 [2½"]	Approx. 0.08 kg [0.18 lb]

Process connection with thread per EN 837-3

NS	G	Dimensions in mm [in]			
		b1 ±1 [0.04]	b2	D	SW
50 [2"]	G 1/8 B	48.5 [1.91]	31 [1.22]	49 [1.93]	14 [0.55]
	G 1/4 B	51.5 [2.03]	31 [1.22]	49 [1.93]	14 [0.55]
63 [2 ½"]	G 1/8 B	48.5 [1.91]	31 [1.22]	62 [2.44]	14 [0.55]
	G 1/4 B	51.5 [2.03]	31 [1.22]	62 [2.44]	14 [0.55]

Process connection with thread per ISO 7 or ANSI/B1.20.1

NS	G	Dimensions in mm [in]				
		b1 ±1 [0.04]	b2	D	SW	
50 [2"]	1/8 NPT	48.5 [1.91]	31 [1.22]	49 [1.93]	14 [0.55]	
	1/4 NPT	51.5 [2.03]	31 [1.22]	49 [1.93]	14 [0.55]	
63 [2 ½"]	1/8 NPT	48.5 [1.91]	31 [1.22]	62 [2.44]	14 [0.55]	
	1/4 NPT	51.5 [2.03]	31 [1.22]	62 [2.44]	14 [0.55]	

Ordering information

Model / Nominal size / Scale range / Connection location / Process connection / Options

© 10/2003 WIKA Alexander Wiegand SE & Co. KG, all rights reserved. The specifications given in this document represent the state of engineering at the time of publishing.

We reserve the right to make modifications to the specifications and materials. In case of a different interpretation of the translated and the English data sheet, the English wording shall prevail.



Page 8 of 8