

# Pressure Transmitters for Low Pressures and Differential Pressures Model DP-10

WIKA Data Sheet PE 81.06

## **Applications**

- Heating, ventilation and air conditioning technology
- Clean room applications
- Medical industry
- Filtering and dedusting applications

## **Special Features**

- Pressure ranges from 0 ... 0.6 mbar to 0 ... 1000 mbar Special pressure range 800 ... 1,200 mbar absolute gauge pressure and vacuum, differential pressure
- Various industrial standard signal outputs
- Output signal calculated by root-evolution
- LCD indication
- 1-2 alarm contacts



#### **Pressure Transmitter model DP-10**

## **Description**

The WIKA pressure transmitters Model DP-10 have been developed for the measurement of low gauge pressures and vacuum, as well as differential pressures. These transmitters are exclusively suitable for dry, clean and nonaggressive gases.

### Measuring principle

The pressure is measured via a sensitive diaphragm, which is adapted to the pressure range, or a capsule element for absolute pressure ranges. An inductive system generates a linear signal which changes in proportion to the prevailing pressure.

#### **Applications**

This transmitter has mainly been designed for HVAC, filtering, dedusting and clean room applications as well as for the medical industry.

For applications in which switching functions are additionally required pressure transmitters with 3 and 4-wire systems can be equipped with up to two alarm contacts. For each alarm contact a potential-free change-over contact is available.

For the local indication of the measured values the pressure transmitters can optionally be equipped with a 3  $\frac{1}{2}$ -digit LCD display.

For flow measurements by means of a standard orifice plate a special design with an output signal calculated by root-evolution is available for 3 and 4-wire systems. With this design it is possible to adjust the suppression of creeping quantities by means of potentiometers in the range 0 ... 10 %.

WIKA Data Sheet PE 81.06 · 07/2009

Page 1 of 4




Specifications	Model DP-10																	
Pressure ranges <sup>1)</sup>	mbar	0.6	1	1.6	2.5	4	16	3   10	16	3 25	40	60		100   160	250	400	600	1000
Over pressure safety	mbar	3	5	8	12.5			30 50	80					500 800				
Maximum static pressure	mbar	1000													1			
Pressure reference	111201	relative pressure, differential pressure, {absolute pressure <sup>2)</sup> from 500 mbar abs; special pressure range 800 1200 mbar abs}																
Pressure connection	mm	two hose connections Ø 6.6 x 11 for hoses with inside Ø 5 6																
Materials		{2 x clamping ring connection G 1/6, Ms}																
■ Wetted parts		Ms, CuBe, PU, Ni																
■ Case		bottom part: ABS, glass fibre reinforced, top part: ABS																
Power supply U <sub>B</sub>	DC V	19 31 {12 30 with signal output 4 20 mA, 2-wire system}																
Tower supply OB	AC V			•			_	•					Зу	Sterriy				
Signal output and Maximum load $\boldsymbol{R}_{\boldsymbol{A}}$		$ \begin{cases} 24,  115 \text{ or } 230 \text{ (respectively } \pm 10 \%,  50  \dots  60  \text{Hz}) \} \\ 0  \dots  10  \text{V},  3\text{-wire system} & \text{R}_{\text{A}} > 2.0  \text{kOhm} \\ \{0  \dots  5  \text{V},  3\text{-wire system} \} & \text{R}_{\text{A}} \leq 2.0  \text{kOhm} \\ \{0  (4)  \dots  20  \text{mA},  3\text{-wire system} \} & \text{R}_{\text{A}} \leq 500  \text{Ohm} \\ \{4  \dots  20  \text{mA},  2\text{-wire system} \} & \text{R}_{\text{A}} \leq (\text{U}_{\text{B}}[\text{V}] - 12  \text{V})  /  0.02  \text{mA} \\ \{\text{other on request} \} \end{cases} $																
Power consumption	mA	≤ 10; (3-/4-wire); (AC-/DC-supply)																
Response time (10 90 %)	ms	approx. 20 {attenuation on request}																
Adjustability zero point / span	% of span	± 5																
Accuracy	% of span	≤ 1.0	) (lim	it poi	nt cali	brati	ior	n) {0.5 o	r 0.2	2 for p	ressu	e rang	je	from 2.5	mbar}			
Hysteresis	% of span	≤ 1.0 (limit point calibration) {0.5 or 0.2 for pressure range from 2.5 mbar} ≤ 0.1																
Repeatability	% of span	≤ 0.05																
1-year stability	% of span	≤ 0.5	at (at	refere	nce c	ondi	itio	ns)										
Permissible temperature of																		
■ Medium	°C	-10 .	+5	0							14	122	٥	F				
■ Ambient	°C	-10 +50 {-10 +60} 14 122 °F (14 140 °F)																
■ Storage	°C	-10 +70 14 158 °F																
Compensated temp. range	°C	+10	+	50							50	122	0	F				
Temperature coefficients in compen	sated temp range:																	
■ Mean TC of zero	% of span/10K	≤ 0.3	3															
■ Mean TC of range	% of span/10K	≤ 0.3																
Shock resistance	g	10																
Suitable media		clean, non-aggressive, dry gases																
Sensor volume	ml	appr	ox. s	ō (app	rox. 7	for	me	easuring	ran	nges <	2.5 n	nbar)						
Increase in volume	ml	appr	ox.	1 at no	omina	l pre	ss	ure										
CE-conformity		Interference emission and immunity see EN 61 326 / A1; declaration of conformity on reque european guideline for low voltages EN 610 10											quest					
{integrated digital indicator}		LC c	lispla	ay, 3 ½	⁄₂-digi	ts; h	eiç	ght of di	gits	10 m	m, pic	k-up ra	at	e 3/sec.				
{Alarm contacts}		only	with	3-wir	e sys	tems	3											
■ Number		1 or	2															
Switching function		standard setting maxalarm																
Adjustability	% of span	1 100																
Switching accuracy	% of span	≤1																
Switching repeatability	% of span	0.2 typical																
Switching hysteresis	% of span	0 10, adjustable																
■ Contacts		1 potential-free relay change-over contact per alarm contact																
■ Contact rating	AC	6 A, 230 V with ohmic load																
{Root-evolved output signal}																		
■ Accuracy	% of span	1.0																
■ Calculation		the root is evolved according to the following equations: $\begin{array}{ll} U_R = \sqrt{(10 \times U_L)} & U_L = \text{linear output 0 10 V} \\ I_R = \sqrt{(20 \times I_L)} & I_L = \text{linear output 0 20 mA} \\ I = 4 + 16 \sqrt{(P/P_{nenn})} & I = \text{linear output 4 20 mA} \\ P = \text{current pressure} \\ P_{nenn} = \text{pressure range} \end{array}$																
Electrical connection		via cable gland PG 7 and internal screw terminals in the bottom part of the case, terminal clamping diameter 1.5 mm <sup>2</sup>												inal				
Ingress of protection					0 529													
Weight	kg	approx. 0.6 (approx. 0.7 with power supply)																
Dimensions	mm			ings	1			1,200		1-1-7								
			for	0														


 <sup>{}</sup> Items in curved brackets are optional extras for additional price.
 1) The measuring ranges 0 ... 0.1 mbar; 0 ... 0.25 mbar; 0 ... 0.4 mbar are available on request.
 For these measuring ranges a larger measuring cell and consequently also a case with larger dimensions is required.

 2) Only with 4 ... 20 mA 2-wire, other output signals on request.

# **Dimensions in mm**



# **Electrical connection**



Specifications and dimensions given in this leaflet represent the state of engineering at the time of printing. Modifications may take place and materials specified may be replaced by others without prior notice.

Page 4 of 4

WIKA Data Sheet PE 81.06 · 07/2009



WIKA Alexander Wiegand SE & Co. KG Alexander-Wiegand-Straße 30

Alexander-Wiegand-Straße 30 63911 Klingenberg/Germany Tel. (+49) 9372/132-0 Fax (+49) 9372/132-406 E-mail info@wika.de

www.wika.de