OBSOLETE

Electrical thermometer with tapered thermowell For shipbuilding industry Models TR293, TC293

WIKA data sheet TE 69.25



Applications

- Exhaust gas temperature measurement in diesel engines and turbines
- For On-, Offshore plants

Special features

- Robust
- Medium temperature to 850 °C with thermocouple, to 600 °C with resistance thermometer
- Approval Lloyd's Register



Description

These model Tx293 electrical thermometers are used for the measurement of exhaust gas temperatures on diesel engines and turbines. The standard temperature range is $0 \dots 850$ °C for thermocouples, $0 \dots 600$ °C for resistance thermometers. The thermowells are designed for the loads which occur in medium and large power plants.

These thermometers are suitable for ambient temperatures to 200 °C. The process connection is made via male connectors, with a standard insertion length of 202 mm.



Page 1 of 4



Resistance thermometer for model TR293

Neck

Sensor tolerance value per DIN EN 60751

Class B

The combination of a 2-wire connection with Class B is not permissible, because the lead resistance of the measuring insert overrides the higher sensor accuracy.

For detailed specifications for Pt100 sensors, see Technical Information IN 00.17 at www.wika.com.

Thermocouple for model TC293

Sensor type

K (NiCr-Ni) Application range up to 850 °C
J (Fe-CuNi) Application range up to 600 °C

Listed thermocouples are available both as single or dual thermocouples. The thermocouple will be delivered with an insulated measuring point.

Tolerance value

For the tolerance value of thermocouples, a cold junction temperature of 0 $^{\circ}$ C has been taken as the basis.

Туре К

Class	Temperature range	Tolerance value		
DIN EN 60584 part 2				
2	-40 +333 °C	± 2.5 °C		
2	+333 +1200 °C	± 0.0075 • t ¹⁾		

1) | t | is the value of the temperature in °C irrespective of the sign.

Type J

Class	Temperature range	Tolerance value
DIN EN 60584	part 2	
2	-40 +333 °C	± 2.5 °C
2	+333 +750 °C	± 0.0075 • t ¹⁾

1) | t | is the value of the temperature in °C irrespective of the sign.

Tolerance value at selected temperatures in °C

Temperature (ITS 90) °C	Tolerance value DIN EN Type K °C	60584 part 2 Type J °C
0	± 2.5	± 2.5
200	± 2.5	± 2.5
400	± 3.0	± 3.0
600	± 4.5	± 4.5
800	± 6.0	undefined

Material Stainless steel 1.4571

Neck length M_H 50, 100 mm others on request

Diameter 15 mm

Process connection

Mode of connection Threaded connection

Material

Stainless steel 1.4571

Thread G ¾ B others on request

Thermowell

Design from solid-machined material, tapered

Material Stainless steel 1.4571

Diameter 23 mm, tapered to 14 mm


Insertion length 100, 150, 202, 250 mm

other versions on request



Dimensions in mm

Model Tx293 with connection head BS



Connection head





BSK


Model	Material	Cable entry	Ingress protection	Сар	Surface finish
BS	Aluminium	M20 x 1.5	IP 54	Cap with 2 screws	Epoxy coated
BSZ	Aluminium	M20 x 1.5	IP 65	Hinged cover with cylinder head screw	Epoxy coated
KNE	Aluminium	M20 x 1.5	IP 65	Screw cover	Epoxy coated
BSK	Plastic	M20 x 1.5	IP 54	Screw cover	not coated

1) Cable gland, metal




Electrical connection

Model TR293



Model TC293



Colour coding

Sensor type	Standard	Positive	Negative
к	DIN EN 60584	green	white
J	DIN EN 60584	black	white

Ordering information

Model / Sensor connection method / Process conenction / Neck length MH / Insertion length U1 / Connection head

© 2003 WIKA Alexander Wiegand SE & Co. KG, all rights reserved. The specifications given in this document represent the state of engineering at the time of publishing. We reserve the right to make modifications to the specifications and materials.

Page 4 of 4

WIKA data sheet TE 69.25 · 05/2014



WIKA Alexander Wiegand SE & Co. KG Alexander-Wiegand-Straße 30 63911 Klingenberg/Germany Tel. +49 9372 132-0 Fax +49 9372 132-406 info@wika.de www.wika.de